



WXF301

**Push button for shutter gallery 2 modules**

**Technical properties**

**Architecture**

Type of order	Switch
Type of control unit	double rocker
Fixing mode	Clipped

**Compatibility**

IFTTT support available	No
-------------------------	----

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 A
---------------	------

**Dimensions**

Depth	34 mm
Height	45 mm
Width	45 mm

**Materials**

Surface appearance	matt
Type of surface treatment	untreated

**Connection**

Connection cross-sect. flexible conductor	1,5 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 2,5mm <sup>2</sup>
Type of connection	Quickconnect

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

Approvals	EN 60669-1
-----------	------------

**Safety**

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes

**Use conditions**

---

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

---

**Identification**

---

Range	gallery
Composition	Middle plate

---