



WXF315

Electronic thermostat gallery

Technical properties

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Rated operational voltage U _e	230 / 250 V
Frequency	50 Hz

Measurement

Range of temperatures	5 / 30 °C
-----------------------	-----------

Capacity

Number of modules for WA	2
--------------------------	---

Power supply

Supply voltage	230 V
----------------	-------

Materials

Material	Polycarbonate (PC)
----------	--------------------

Installation, mounting

Mounting type	flush-mounted
---------------	---------------

Connection

Type of connection	Screw connection
--------------------	------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	0...50 °C
Storage/transport temperature	-20...60 °C
Energy efficiency class	IV (2%)

Identification

Application, usage	HVAC control
--------------------	--------------