



WXF315

## Electronic thermostat gallery

### Technical properties

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Main electrical features

Rated operational voltage Ue	230 / 250 V
Frequency	50 Hz

#### Measurement

Range of temperatures	5 / 30 °C
-----------------------	-----------

#### Capacity

Number of modules for WA	2
--------------------------	---

#### Power supply

Supply voltage	230 V
----------------	-------

#### Connection

Type of connection	Screw connection
--------------------	------------------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	0...50 °C
Storage/transport temperature	-20...60 °C
Energy efficiency class	IV (2%)

#### Identification

Application, usage	HVAC control
Range	gallery