



WXF315

**Electronic thermostat gallery**

**Technical properties**

**Controls and indicators**

Indicator lamp	yes
----------------	-----

**Main electrical features**

Rated operational voltage Ue	230 / 250 V
Frequency	50 Hz

**Measurement**

Range of temperatures	5 / 30 °C
-----------------------	-----------

**Capacity**

Number of modules for WA	2
--------------------------	---

**Power supply**

Supply voltage	230 V
----------------	-------

**Installation, mounting**

Mounting type	flush-mounted
---------------	---------------

**Connection**

Type of connection	Screw connection
--------------------	------------------

**Use conditions**

Operating temperature	0...50 °C
Storage/transport temperature	-20...60 °C

Temperature	Temperature measurement via internal temperature sensor
-------------	---

Energy efficiency class	IV (2%)
-------------------------	---------

**Identification**

Application, usage	HVAC control
--------------------	--------------

Range	gallery
-------	---------