



WXF316

Pilot thermostat wire gallery

Technical properties

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Rated operational voltage Ue	230 / 250 V
Frequency	50 Hz

Dimensions

Width of installed product	45 mm
----------------------------	-------

Measurement

Range of temperatures	5 / 30 °C
-----------------------	-----------

Capacity

Number of modules for WA	2
--------------------------	---

Power supply

Supply voltage	230 V
----------------	-------

Materials

Colour	white
--------	-------

Installation, mounting

Mounting type	flush-mounted
---------------	---------------

Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm ²
Connection cross-sect. rigid cable	1,5 / 2,5mm ²
Type of connection	Screw connection

Use conditions

Operating temperature	0...50 °C
Storage/transport temperature	-20...60 °C
Temperature	additional connection for external temperature sensor
Energy efficiency class	IV (2%)

Identification

Application, usage	HVAC control
Range	gallery