



WXF316

Pilot thermostat wire gallery

Technical properties

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Rated operational voltage Ue	230 / 250 V
Frequency	50 Hz

Dimensions

Width of installed product	45 mm
----------------------------	-------

Measurement

Range of temperatures	5 / 30 °C
-----------------------	-----------

Capacity

Number of modules for WA	2
--------------------------	---

Power supply

Supply voltage	230 V
----------------	-------

Materials

Colour	white
--------	-------

Connection

Type of connection	Screw connection
--------------------	------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	0...50 °C
Storage/transport temperature	-20...60 °C

Temperature	additional connection for external temperature sensor
-------------	---

Energy efficiency class	IV (2%)
-------------------------	---------

Identification

Application, usage	HVAC control
Range	gallery