



WXF421V

**Socket for trunking gallery 2P+E 16A green**

**Technical properties**

**Architecture**

Type of pole	2P+T
--------------	------

**Configuration**

Number of modules	3
-------------------	---

**Main electrical features**

Nominal voltage	250 V
-----------------	-------

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Depth	45 mm
-------	-------

Height	43.5 mm
--------	---------

Width	67.5 mm
-------	---------

**Cover, door**

Cover	Complete housing
-------	------------------

**Materials**

Colour	green
--------	-------

Material	Polycarbonate (PC)
----------	--------------------

Type of surface treatment	untreated
---------------------------	-----------

**Connection**

Type of connection	Quickconnect
--------------------	--------------

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

Approvals	NFC 61314
-----------	-----------

European directive WEEE	concerned
-------------------------	-----------

**Safety**

IK protection code against mechanical impacts	07
---	----

Protection index IP	IP20
---------------------	------

Protection	Enhanced contact protection
------------	-----------------------------

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C