



WXF422B

**Double socket for trunking gallery 2P+E 16A pure**

**Technical properties**

**Architecture**

Type of order	Socket
Type of pole	2P+T

**Configuration**

Number of modules	4
-------------------	---

**Main electrical features**

Nominal voltage	250 V
-----------------	-------

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Depth	45 mm
Height	42.5 mm
Width	90 mm

**Cover, door**

Cover	Complete housing
-------	------------------

**Materials**

Free area for finishing name	pure
Colour	white
Surface appearance	glossy
Type of surface treatment	untreated

**Connection**

Connection cross-sect. flexible conductor	1,5 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of connection	Quickconnect

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

Approvals	NFC 61314
-----------	-----------

**Safety**

IK protection code against mechanical impacts	07
REACH conform	Yes

RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection
<b>Use conditions</b>	
Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C
<b>Identification</b>	
Range	gallery
Composition	Mechanism with upper casing