



WXF422B

## Double socket for trunking gallery 2P+E 16A pure

### Technical properties

#### Configuration

Number of modules 4

#### Main electrical features

Nominal voltage 250 V

#### Electric current

Rated current 16 A

#### Dimensions

Depth 45 mm

Height 42.5 mm

Width 90 mm

#### Cover, door

Cover Complete housing

#### Materials

Free area for finishing name pure

Colour white

Type of surface treatment untreated

#### Connection

Type of connection Quickconnect

#### Equipment

With transparent product label holder No

#### Standards

European directive WEEE concerned

#### Safety

IK protection code against mechanical impacts 07

Protection index IP IP20

Protection Enhanced contact protection

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

