



WXF422R

Double socket for trunking gallery 2P+E 16A red

Technical properties

Architecture

| | |
|---------------|--------|
| Type of order | Socket |
| Type of pole | 2P+T |

Configuration

| | |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

Main electrical features

| | |
|-----------------|-------|
| Nominal voltage | 250 V |
|-----------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Dimensions

| | |
|--------|---------|
| Depth | 45 mm |
| Height | 42.5 mm |
| Width | 90 mm |

Cover, door

| | |
|-------|------------------|
| Cover | Complete housing |
|-------|------------------|

Materials

| | |
|------------------------------|-----------|
| Free area for finishing name | red |
| Surface appearance | glossy |
| Type of surface treatment | untreated |

Connection

| | |
|---|---|
| Connection cross-sect. flexible conductor | 1,5 / 2,5mm ² |
| Connection cross-sect. rigid cable | mini 2x1 mm ² - maxi 2x2,5 mm ² |
| Type of connection | Quickconnect |

Equipment

| | |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

Standards

| | |
|-----------|-----------|
| Approvals | NFC 61314 |
|-----------|-----------|

Safety

| | |
|---|-----------------------------|
| IK protection code against mechanical impacts | 07 |
| Protection | Enhanced contact protection |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

Identification

| | |
|-------------|-----------------------------|
| Range | gallery |
| Composition | Mechanism with upper casing |
