



WXF422R

Double socket for trunking gallery 2P+E 16A red

Technical properties

Configuration

Number of modules 4

Main electrical features

Nominal voltage 250 V

Electric current

Rated current 16 A

Dimensions

Depth 45 mm

Height 42.5 mm

Width 90 mm

Cover, door

Cover Complete housing

Materials

Free area for finishing name red

Type of surface treatment untreated

Connection

Type of connection Quickconnect

Equipment

With transparent product label holder No

Standards

European directive WEEE concerned

Safety

IK protection code against mechanical impacts 07

Protection index IP IP20

Protection Enhanced contact protection

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

