



WXF423R

Triple socket for trunking gallery 2P+E 16A red

Technical properties

Architecture

Type of pole	2P+T
--------------	------

Configuration

Number of modules	6
-------------------	---

Main electrical features

Nominal voltage	250 V
-----------------	-------

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth	45 mm
Height	42.5 mm
Width	135 mm

Cover, door

Cover	Complete housing
-------	------------------

Materials

Type of surface treatment	untreated
---------------------------	-----------

Connection

Type of connection	Quickconnect
--------------------	--------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals	NFC 61314
European directive WEEE	concerned

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP20
Protection	Enhanced contact protection

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

