



WXF423T

Triple socket for trunking gallery 2P+E 16A titane

Technical properties

Architecture

Type of order	Socket
Type of pole	2P+T

Configuration

Number of modules	6
-------------------	---

Main electrical features

Nominal voltage	250 V
-----------------	-------

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth	45 mm
Height	42.5 mm
Width	135 mm

Cover, door

Cover	Complete housing
-------	------------------

Materials

Surface appearance	satın finish
--------------------	--------------

Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm ²
Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of connection	Quickconnect

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals	NFC 61314
-----------	-----------

Safety

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Protection	Enhanced contact protection

Use conditions

Operating temperature

-10...35 °C

Storage/transport temperature

-10...50 °C

Identification

Composition

Mechanism with upper casing