



WXF432

**Double socket with detrompage for trunking gallery 2P+E 16A**

**Technical properties**

**Configuration**

Number of modules 4

**Main electrical features**

Nominal voltage 250 V

**Electric current**

Rated current 16 A

**Dimensions**

Depth 45 mm

Height 42.5 mm

Width 90 mm

**Cover, door**

Cover Complete housing

**Materials**

Surface appearance matt

Type of surface treatment untreated

**Connection**

Type of connection Quickconnect

**Equipment**

With transparent product label holder No

**Standards**

European directive WEEE concerned

**Safety**

IK protection code against mechanical impacts 07

Protection index IP IP20

Protection Enhanced contact protection

**Use conditions**

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

**Identification**

Range gallery

