



WXF433

## Triple socket with detrompage for trunking gallery 2P+E 16A

### Technical properties

#### Architecture

Type of pole	2P+T
--------------	------

#### Configuration

Number of modules	6
-------------------	---

#### Main electrical features

Nominal voltage	250 V
-----------------	-------

#### Electric current

Rated current	16 A
---------------	------

#### Dimensions

Depth	45 mm
Height	42.5 mm
Width	135 mm

#### Cover, door

Cover	Complete housing
-------	------------------

#### Materials

Material	Polycarbonate (PC)
Surface appearance	matt
Type of surface treatment	untreated

#### Connection

Type of connection	Quickconnect
--------------------	--------------

#### Equipment

With transparent product label holder	No
---------------------------------------	----

#### Standards

Approvals	NFC 61314
European directive WEEE	concerned

#### Safety

IK protection code against mechanical impacts	07
Protection index IP	IP20
Protection	Enhanced contact protection

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C