



WXF436B

Switch 16AX multi sockets gallery 2P+E pure

Technical properties

Architecture

Type of control unit	single rocker
Fixing mode	Clipped

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 AX
---------------	-------

Dimensions

Depth	52 mm
Insertion depth	52 mm
Height	45 mm
Width	45 mm

Materials

Free area for finishing name	pure
Colour	white
Type of surface treatment	untreated

Connection

Type of connection	Quickconnect
--------------------	--------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	05
---	----

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C
Identification	
Range	gallery
Composition	Mechanism with upper casing