



WXF436B

Switch 16AX multi sockets gallery 2P+E pure

Technical properties

Architecture

Type of order	Switch
Type of pole	2P+T
Type of control unit	single rocker
Fixing mode	Clipped

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 AX
---------------	-------

Dimensions

Depth	52 mm
Insertion depth	52 mm
Height	45 mm
Width	45 mm

Materials

Free area for finishing name	pure
Colour	white
Surface appearance	glossy
Type of surface treatment	untreated

Connection

Connection cross-sect. flexible conductor	0,5 / 2,5mm ²
Connection cross-sect. rigid cable	0,5 / 2,5mm ²
Type of connection	Quickconnect

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts

05

Use conditions

Operating temperature

-10...35 °C

Storage/transport temperature

-10...50 °C

Identification

Range

gallery

Composition

Mechanism with upper casing