



WXF601

Indicator gallery red et green 2 modules

Technical properties

Architecture

Fixing mode Clipped

Main electrical features

Nominal voltage 250 V

Dimensions

Depth 41.2 mm

Height 45 mm

Width 45 mm

Power

Max. power per charging point 1.4 W

Capacity

Number of sockets 1

Materials

Surface appearance glossy

Type of surface treatment untreated

Lighting control

Type of lamp LED

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Mechanism with upper casing