



WXF602

**Indicator gallery blue 2 modules**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Main electrical features**

Nominal voltage 250 V

**Dimensions**

Depth 41.2 mm

Height 45 mm

Width 45 mm

**Power**

Max. power per charging point 1.6 W

**Capacity**

Number of sockets 1

**Materials**

Colour dark grey

RAL colour RAL 7011 - Iron grey

Material Plastic/metal

Type of surface treatment untreated

**Lighting control**

Type of lamp LED

**Standards**

European directive WEEE concerned

**Safety**

IK protection code against mechanical impacts 05

**Use conditions**

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

**Identification**

Range gallery

Composition Mechanism with upper casing