



WXF602

Indicator gallery blue 2 modules

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Main electrical features

Nominal voltage	250 V
-----------------	-------

Dimensions

Depth	41.2 mm
Height	45 mm
Width	45 mm

Power

Max. power per charging point	1.6 W
-------------------------------	-------

Capacity

Number of sockets	1
-------------------	---

Materials

Surface appearance	glossy
Type of surface treatment	untreated

Lighting control

Type of lamp	LED
--------------	-----

Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	Mechanism with upper casing