



WXF603

Indicator gallery white 2 modules

Technical properties

Architecture

Fixing mode Clipped

Main electrical features

Nominal voltage 250 V

Dimensions

Depth 41.2 mm

Height 45 mm

Width 45 mm

Power

Max. power per charging point 1.6 W

Capacity

Number of sockets 1

Materials

Colour dark grey

RAL colour RAL 7011 - Iron grey

Material Plastic/metal

Type of surface treatment untreated

Lighting control

Type of lamp LED

Standards

European directive WEEE concerned

Safety

IK protection code against mechanical impacts 05

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Mechanism with upper casing