



WXF610

Emergency stop switch gallery with key

Technical properties

Architecture

Type of control unit	Key
Fixing mode	Clipped

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth	40 mm
Height	45 mm
Width	45 mm

Materials

Colour	dark grey
RAL colour	RAL 7011 - Iron grey
Material	Plastic/metal
Surface appearance	matt
Type of surface treatment	untreated

Connection

Type of connection	Screw connection
--------------------	------------------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	IK02
Protection index IP	IP20

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature

-10...50 °C

Identification

Range

gallery

Composition

Middle plate