



WXF611

Emergency switch gallery 1/4 turn 2 modules

Technical properties

Architecture

Type of control unit	Key
Fixing mode	Clipped

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth	40 mm
Height	45 mm
Width	45 mm

Materials

Surface appearance	matt
Type of surface treatment	untreated

Connection

Type of connection	Screw connection
--------------------	------------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Safety

IK protection code against mechanical impacts	IK02
---	------

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
-------	---------

