



WXF611

**Emergency switch gallery 1/4 turn 2 modules**

**Technical properties**

**Architecture**

Type of control unit	Key
Fixing mode	Clipped

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Compatibility**

IFTTT support available	No
-------------------------	----

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Depth	40 mm
Height	45 mm
Width	45 mm

**Materials**

Surface appearance	matt
Type of surface treatment	untreated

**Connection**

Type of connection	Screw connection
--------------------	------------------

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Safety**

IK protection code against mechanical impacts	IK02
---	------

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

**Identification**

Range	gallery
-------	---------

