



WXF615B

**Key switch gallery 2 positions 2 modules pure-white**

**Technical properties**

**Architecture**

Type of control unit	Key
Fixing mode	Clipped

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Compatibility**

IFTTT support available	No
-------------------------	----

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Depth	51.3 mm
Insertion depth	34 mm
Height	45 mm
Width	45 mm

**Materials**

Free area for finishing name	pure
Colour	white
Surface appearance	glossy
Type of surface treatment	untreated

**Connection**

Type of connection	Screw connection
--------------------	------------------

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Safety**

IK protection code against mechanical impacts	IK02
REACH conform	Yes
RoHS conform	Yes

**Use conditions**

---

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

---

**Identification**

---

Range	gallery
Composition	Basic element with central cover plate

---