



WXF615T

## Key switch gallery 2 positions 2 modules titane

### Technical properties

#### Architecture

Type of control unit	Key
Fixing mode	Clipped

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

#### Electric current

Rated current	10 A
---------------	------

#### Dimensions

Depth	51.3 mm
Insertion depth	34 mm
Height	45 mm
Width	45 mm

#### Materials

Free area for finishing name	titane
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material	Plastic/metal
Surface appearance	satin finish
Type of surface treatment	Painted

#### Connection

Type of connection	Screw connection
--------------------	------------------

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

IK protection code against mechanical impacts	IK02
Protection index IP	IP20

REACH conform	Yes
RoHS conform	Yes
<b>Use conditions</b>	
Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C
<b>Identification</b>	
Composition	Basic element with central cover plate