



WXF616N

## Key switch gallery 3 positions 2 modules night

### Technical properties

#### Architecture

Type of control unit	Key
Fixing mode	Clipped

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

#### Electric current

Rated current	1.2 A
---------------	-------

#### Dimensions

Depth	51.3 mm
Insertion depth	34 mm
Height	45 mm
Width	45 mm

#### Materials

Free area for finishing name	night
Surface appearance	satín finish

#### Connection

Type of connection	Screw connection
--------------------	------------------

#### Safety

IK protection code against mechanical impacts	IK02
REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

#### Identification

Range	gallery
-------	---------

