



WXF617N

Key switch gallery 3 positions extraction in 0 night

Technical properties

Architecture

Type of control unit	Key
Fixing mode	Clipped

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth	51.3 mm
Insertion depth	34 mm
Height	45 mm
Width	45 mm

Materials

Free area for finishing name	night
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	Polycarbonate (PC)
Surface appearance	satın finish
Type of surface treatment	Painted

Connection

Type of connection	Screw connection
--------------------	------------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	IK02
Protection index IP	IP20
Use conditions	
Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C
Identification	
Range	gallery
Composition	Basic element with central cover plate