



WXF617T

Key switch gallery 3 positions extraction in 0 titane

Technical properties

Architecture

Type of control unit	Key
Fixing mode	Clipped

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth	51.3 mm
Insertion depth	34 mm
Height	45 mm
Width	45 mm

Materials

Free area for finishing name	titane
Surface appearance	satın finish

Connection

Type of connection	Screw connection
--------------------	------------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Safety

IK protection code against mechanical impacts	IK02
---	------

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range

gallery

Composition

Basic element with central cover plate