



WXF624

## XLR male gallery neutral connector

### Technical properties

#### Connectivity

|        |                      |
|--------|----------------------|
| Outlet | with straight outlet |
|--------|----------------------|

#### Dimensions

|        |         |
|--------|---------|
| Depth  | 31.5 mm |
| Height | 45 mm   |
| Width  | 45 mm   |

#### Capacity

|                   |   |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

#### Materials

|                           |           |
|---------------------------|-----------|
| Surface appearance        | matt      |
| Type of surface treatment | untreated |

#### Safety

|   |      |
|---|------|
| IK protection code against mechanical impacts | IK02 |
| REACH conform                                 | Yes  |
| RoHS conform                                  | Yes  |

#### Use conditions

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

#### Identification

|             |              |
|-------------|--------------|
| Range       | gallery      |
| Composition | Middle plate |