



WXF631

RCA audio/video screw terminal 2M

Technical properties

Connectivity

Outlet with straight outlet

Dimensions

Depth 39.4 mm

Height 45 mm

Width 45 mm

Capacity

Number of sockets 1

Materials

Surface appearance matt

Type of surface treatment untreated

Equipment

Supporting plate / Supporting ring without supporting ring

Safety

IK protection code against mechanical impacts IK02

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Middle plate