



WXF641

**SUB-D15 (VGA+minijack) gallery screw ter**

**Technical properties**

**Connectivity**

Outlet with straight outlet

**Dimensions**

Depth 34.7 mm  
 Height 45 mm  
 Width 45 mm

**Capacity**

Number of sockets 1

**Materials**

Surface appearance matt  
 Type of surface treatment untreated

**Equipment**

Supporting plate / Supporting ring without supporting ring

**Safety**

IK protection code against mechanical impacts IK02  
 REACH conform Yes  
 RoHS conform Yes

**Use conditions**

Operating temperature -10...35 °C  
 Storage/transport temperature -10...50 °C

**Identification**

Range gallery  
 Composition Middle plate