



WXF641

## SUB-D15 (VGA+minijack) gallery screw ter

### Technical properties

#### Connectivity

Outlet	with straight outlet
--------	----------------------

#### Dimensions

Depth	34.7 mm
Height	45 mm
Width	45 mm

#### Capacity

Number of sockets	1
-------------------	---

#### Materials

RAL colour	RAL 7011 - Iron grey
Material	Polycarbonate (PC)
Surface appearance	matt
Type of surface treatment	untreated

#### Equipment

Supporting plate / Supporting ring	without supporting ring
------------------------------------	-------------------------

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

IK protection code against mechanical impacts	IK02
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C