



WXF645

Optic socket gallery passthrough SC 2 modules

Technical properties

Connectivity

Outlet with straight outlet

Dimensions

Depth 31 mm

Capacity

Number of sockets 1

Number of module locations 2

Materials

Surface appearance matt

Type of surface treatment untreated

Equipment

Supporting plate / Supporting ring without supporting ring

Safety

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -10...35 °C

Identification

Range gallery

Composition Middle plate