



WXF646

## Optic socket gallery passthrough LC 2 modules

### Technical properties

#### Connectivity

Outlet with straight outlet

#### Dimensions

Depth 29.25 mm

#### Capacity

Number of sockets 1

Number of module locations 2

#### Materials

Surface appearance matt

Type of surface treatment untreated

#### Equipment

Supporting plate / Supporting ring without supporting ring

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -10...35 °C

#### Identification

Range gallery

Composition Middle plate