



WXF646

## Optic socket gallery passthrough LC 2 modules

### Technical properties

#### Connectivity

Outlet	with straight outlet
--------	----------------------

#### Dimensions

Depth	29.25 mm
-------	----------

#### Capacity

Number of sockets	1
Number of module locations	2

#### Materials

Material	Polycarbonate (PC)
Surface appearance	matt
Type of surface treatment	untreated

#### Equipment

Supporting plate / Supporting ring	without supporting ring
------------------------------------	-------------------------

#### Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------