



WXF687B

## Wire outlet gallery 1 module pure-white

### Technical properties

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Dimensions

Depth	29.5 mm
-------	---------

Height	45 mm
--------	-------

Width	22.5 mm
-------	---------

#### Materials

Free area for finishing name	pure
------------------------------	------

Colour	white
--------	-------

Type of surface treatment	untreated
---------------------------	-----------

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

IK protection code against mechanical impacts	IK02
---	------

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

#### Identification

Range	gallery
-------	---------

Composition	Basic element with central cover plate
-------------	--

With imprint	No
--------------	----