



WXF687D

### Wire outlet gallery 1 module dune

#### Technical properties

##### Architecture

Fixing mode	Clipped
-------------	---------

##### Dimensions

Depth	29.5 mm
-------	---------

Height	45 mm
--------	-------

Width	22.5 mm
-------	---------

##### Materials

Free area for finishing name	dune
------------------------------	------

RAL colour	RAL 1013 - Oyster white
------------	-------------------------

Type of surface treatment	untreated
---------------------------	-----------

##### Standards

European directive WEEE	concerned
-------------------------	-----------

##### Safety

IK protection code against mechanical impacts	IK02
---	------

Protection index IP	IP20
---------------------	------

##### Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

##### Identification

Range	gallery
-------	---------

Composition	Basic element with central cover plate
-------------	--

With imprint	No
--------------	----