



WXF687T

Wire outlet gallery 1 module titane

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	29.5 mm
-------	---------

Height	45 mm
--------	-------

Width	22.5 mm
-------	---------

Materials

Free area for finishing name	titane
------------------------------	--------

Surface appearance	satın finish
--------------------	--------------

Safety

IK protection code against mechanical impacts	IK02
---	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

Identification

Range	gallery
-------	---------

Composition	Basic element with central cover plate
-------------	--

With imprint	No
--------------	----