



WXF687T

Wire outlet gallery 1 module titane

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 29.5 mm

Height 45 mm

Width 22.5 mm

Materials

Free area for finishing name titane

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Type of surface treatment Painted

Standards

European directive WEEE concerned

Safety

IK protection code against mechanical impacts IK02

Protection index IP IP20

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Basic element with central cover plate

With imprint No