



WXF688B

Blank function gallery 1 module pure-white

Technical properties

Architecture

| | |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

Dimensions

| | |
|--------|---------|
| Depth | 29.5 mm |
| Height | 45 mm |
| Width | 22.5 mm |

Materials

| | |
|------------------------------|-----------|
| Free area for finishing name | pure |
| Colour | white |
| Surface appearance | glossy |
| Type of surface treatment | untreated |

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|---|------|
| IK protection code against mechanical impacts | IK02 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

Identification

| | |
|--------------|---------|
| Range | gallery |
| Composition | other |
| With imprint | No |