



WXF688D

Blank function gallery 1 module dune

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	29.5 mm
-------	---------

Height	45 mm
--------	-------

Width	22.5 mm
-------	---------

Capacity

Number of sockets	1
-------------------	---

Materials

Free area for finishing name	dune
------------------------------	------

Colour	dune
--------	------

RAL colour	RAL 1013 - Oyster white
------------	-------------------------

Material	Polycarbonate (PC)
----------	--------------------

Surface appearance	glossy
--------------------	--------

Type of surface treatment	untreated
---------------------------	-----------

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK02
---	------

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

Identification

Range	gallery
-------	---------

Composition	other
-------------	-------

With imprint	No
--------------	----