



WXF688D

Blank function gallery 1 module dune

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	29.5 mm
-------	---------

Height	45 mm
--------	-------

Width	22.5 mm
-------	---------

Capacity

Number of sockets	1
-------------------	---

Materials

Free area for finishing name	dune
------------------------------	------

Surface appearance	glossy
--------------------	--------

Type of surface treatment	untreated
---------------------------	-----------

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK02
---	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

Identification

Range	gallery
-------	---------

Composition	other
-------------	-------

With imprint	No
--------------	----