



WXF688H

Blank function gallery 1 module pure-white

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	29.5 mm
Height	45 mm
Width	22.5 mm

Materials

Free area for finishing name	antibactérien
Colour	white
Surface appearance	glossy
Type of surface treatment	untreated

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK02
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	other
With imprint	No