



WXF689B

**Blank function gallery 2 modules pure-white**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Dimensions**

Depth 24 mm

Height 45 mm

Width 45 mm

**Capacity**

Number of sockets 3

**Materials**

Free area for finishing name pure

Colour white

Surface appearance glossy

Type of surface treatment untreated

**Standards**

European directive WEEE not concerned

**Safety**

IK protection code against mechanical impacts IK02

**Use conditions**

Operating temperature -10...35 °C

**Identification**

Range gallery

Composition other