



WXF689T

## Blank function gallery 2 modules titane

### Technical properties

#### Architecture

Fixing mode Clipped

#### Dimensions

Depth 24 mm

Height 45 mm

Width 45 mm

#### Capacity

Number of sockets 1

#### Materials

Free area for finishing name titane

Surface appearance satin finish

#### Standards

European directive WEEE not concerned

#### Safety

IK protection code against mechanical impacts IK02

REACH conform Yes

RoHS conform Yes

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Range gallery

Composition other

With imprint No