



WXP0001

## Plate gallery plastic 1 module pure-white

### Technical properties

#### Architecture

|             |         |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

#### Dimensions

|        |        |
|--------|--------|
| Depth  | 9.3 mm |
| Height | 80 mm  |
| Width  | 40 mm  |

#### Capacity

|                   |   |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

#### Materials

|                              |           |
|------------------------------|-----------|
| Free area for finishing name | pure      |
| Colour                       | white     |
| Surface appearance           | glossy    |
| Type of surface treatment    | untreated |

#### Installation, mounting

|              |            |
|--------------|------------|
| Mounting way | horizontal |
|--------------|------------|

#### Equipment

|                                       |    |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

#### Standards

|                         |               |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

#### Safety

|   |     |
|---|-----|
| IK protection code against mechanical impacts | 05  |
| REACH conform                                 | Yes |
| RoHS conform                                  | Yes |

#### Use conditions

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

#### Identification

|             |                       |
|-------------|-----------------------|
| Range       | gallery               |
| Composition | Surface mounted frame |