



WXP0004

**Plate gallery plastic 4 modules enteraxe 71mm pure-white**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Dimensions**

Depth	9.3 mm
Height	88 mm
Width	163 mm

**Capacity**

Number of sockets	1
-------------------	---

**Materials**

Free area for finishing name	pure
Colour	white
Surface appearance	glossy
Type of surface treatment	untreated

**Installation, mounting**

Mounting way	horizontal
--------------	------------

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

**Identification**

Range	gallery
Composition	Surface mounted frame