



WXP0005

Plate gallery plastic 5 modules enteraxe 71mm pure-white

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	9.3 mm
Height	88 mm
Width	163 mm

Capacity

Number of sockets	1
-------------------	---

Materials

Free area for finishing name	pure
Colour	white
Surface appearance	glossy
Type of surface treatment	untreated

Installation, mounting

Mounting way	horizontal
--------------	------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	Surface mounted frame