



WXP0006

Plate gallery plastic 6 modules enteraxe 57mm pure-white

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 9.3 mm

Height 88 mm

Width 206 mm

Capacity

Number of sockets 1

Materials

Free area for finishing name pure

Colour white

RAL colour RAL 9016 - Traffic white

Material Polycarbonate (PC)

Surface appearance glossy

Type of surface treatment untreated

Installation, mounting

Mounting way horizontal

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Protection index IP IP21

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Surface mounted frame